

# Home Care Technical Specification


## 1 1/2" Grab Bars – Concealed Screw

8900

### Stock Numbers:

- ❑ **8912, R8912W – 12" Grab Bar**  
Satin Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **R8916, R8916W – 16" Grab Bar**  
Satin or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **R8918, R8918W, LR8918W – 18" Grab Bar**  
Satin or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **R8924, R8924W, LR8924W – 24" Grab Bar**  
Satin or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **R8930, R8930W – 30" Grab Bar**  
Satin or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **R8932, R8932W – 32" Grab Bar**  
Satin Finish, White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **R8936, R8936W – 36" Grab Bar**  
Satin or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **8942, R8942W – 42" Grab Bar**  
Satin or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **DN8948, R8948W – 48" Grab Bar**  
Satin Finish, White Finish  
1 1/2" Bar, Concealed Screw Mounting

### Dimensions:



	A	B	C
8912	12"	8.175	15.25
8916	16"	12.175	19.25
8918	18"	14.175	21.25
8924	24"	20.175	27.25
8930	30"	26.175	33.25
8932	32"	28.175	35.25
8936	36"	32.175	39.25
8942	42"	38.175	45.25
8948	48"	44.175	51.25

### Materials:

1 1/2" **grab bar** rods are formed from type 304 stainless steel tubing.  
**12" – 42"** length is 20 gauge  
**48"** length is 18 gauge

### Compliance:

- ADA, ANSI, ASTM, CSA
- Tested to 500 lbs. pull

### Installation Instructions:

1. Position unit on wall in desired location.
2. Mark mounting holes.
3. Drill starter holes.
4. Mount unit on wall using 2" screws (provided).
5. Snap flange covers into place.

Note: SecureMount Anchors are recommended for use in non-stud (hollow-wall) applications per installation instructions.

**Stock Number:** \_\_\_\_\_ 1 1/2" Grab Bars  
 By Moen, Inc.



Buy it for looks. Buy it for life.®